



OMEGA³ YARD 300

Power source	10001351	1.10
Front panel	10001371	1.05
Welding programs	10645900	Same as Galaxy

Date	Power source 10001351	Front panel 10001371
19-06-2018	1.10 (B10) <ul style="list-style-type: none"> Start performance has been improved. Soft-start maximum value is now limited to 18 m/min. 	1.05 (B5) <ul style="list-style-type: none"> Date and time settings are now available. Gas test while machine is locked is now possible.
23-03-2017	1.09 (B9) <ul style="list-style-type: none"> E12-04 will not show when internal SD is missing or has bad connection. E24-10 is shown when SD card is missing now. Better encoder reading is giving more accurate and smooth adjustment of current and voltage. 	1.04 (B4) <ul style="list-style-type: none"> No change.
21-12-2016	1.08 (B8) <ul style="list-style-type: none"> E14-11 is not shown after an accidentally power off. Trim voltage on front panel can no longer be adjusted while an analog remote control is connected. Test protocol for production test is implemented. 	1.04 (B4) <ul style="list-style-type: none"> No change.
18-02-2016	1.07 (B7) <ul style="list-style-type: none"> Bug removed: When using the torch trigger switch, for shifting between 2 sequences, an error could occur when one sequence was set to DC and the other sequence was set to Pulse. 	1.04 (B4) <ul style="list-style-type: none"> "Globular LED" was not indicating the correct information when welding with maximum current.
18-12-2015	1.06 (B6) <ul style="list-style-type: none"> Bug fix: Manual MIG program could increase welding voltage to maximum in some circumstances. 	1.03 (B3) <ul style="list-style-type: none"> No change
27-11-2015	1.05 (B5) <ul style="list-style-type: none"> Synergic and Pulse boxes are supported. 	1.03 (B3) <ul style="list-style-type: none"> Synergic and Pulse boxes are supported. change in menu order when showing version numbers and license: Lic: show license information 1: Front panel software version 2: Welding program version

OMEGA³ YARD 300

		3: is control software
18-08-2015	1.02 (B2) <ul style="list-style-type: none">• Compatibility to program package 10645900 version B8 is implemented.	1.00 (B0) <ul style="list-style-type: none">• No change
15-07-2015	1.01 (B1) <ul style="list-style-type: none">• Handling of welding at lower currents improved.	1.00 (B0) <ul style="list-style-type: none">• No change
01-06-2015	1.00 (B0) <ul style="list-style-type: none">• First release.	1.00 (B0) <ul style="list-style-type: none">• First release